


DIMENSIONS: mm (in.)
SPECIFICATIONS

MOUSER PART NO.	A	B	C	Body Color	Line Color	Shaft Hole
450-SL2112	24 (.945)	15 (.591)	11.3 (.445)	Red	Black	1.2x8
450-SL2212	24 (.945)	15 (.591)	11.3 (.445)	Yellow	Black	1.2x8
450-SL2312	24 (.945)	15 (.591)	11.3 (.445)	Blue	Black	1.2x8
450-SL2412	24 (.945)	15 (.591)	11.3 (.445)	Green	Black	1.2x8
450-SL2512	24 (.945)	15 (.591)	11.3 (.445)	Gray	Black	1.2x8
450-SL2612	24 (.945)	15 (.591)	11.3 (.445)	Black	White	1.2x8
450-SL4514	26 (1.02)	11 (.433)	11.8 (.465)	Gray	Black	1.2x4
450-SL4512	26 (1.02)	11 (.433)	11.8 (.465)	Gray	Black	1.2x8
450-SL5512	24 (.945)	9 (.354)	10.8 (.425)	Gray	Black	1.2x4
450-SL6112	24.2 (.953)	11.5 (.453)	10.3 (.406)	Red	White	1.2x18
450-SL6312	24.2 (.953)	11.5 (.453)	10.3 (.406)	Blue	White	1.2x18
450-SL6512	24.2 (.953)	11.5 (.453)	10.3 (.406)	Gray	Black	1.2x18
450-SL6612	24.2 (.953)	11.5 (.453)	10.3 (.406)	Black	White	1.2x18
450-SL6712	24.2 (.953)	11.5 (.453)	10.3 (.406)	White	Black	1.2x18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eagle Plastic Devices:

[450-SL4512](#) [450-SL6712](#) [450-SL2612](#) [450-SL2412](#) [450-SL2312](#) [450-SL5512](#) [450-SL2112](#) [450-SL2212](#) [450-SL6312](#) [450-SL2512](#) [450-SL4514](#) [450-SL6112](#) [450-SL6612](#) [450-SL6512](#) [450-SL4510](#) [450-SL4511](#) [450-SL6112](#) [450-SL6312](#) [450-SL6512](#) [450-SL6612](#) [450-SL6712](#) [450-SL2112](#) [450-SL2212](#) [450-SL2312](#) [450-SL2412](#) [450-SL2512](#) [450-SL4512](#)