



Features

- Fanless system with IBASE MB220 customized board
- Supports 7th/6th Gen Intel® Core™ i7/i5/i3 processors
- Supports three independent display outputs
- Flexible expansion slot system
- Dual SIM slot support WWAN redundancy
- 12V to 24V DC wide-range voltage input
- Over/Under/Reverse voltage protection
- iSMART, iAMT (11.6), TPM (2.0)

Specifications

System Mainboard	MB220AF with Intel® Q170 PCH MB220EF with Intel® H110 PCH
CPU Type	7th/6th Gen Intel® Core™ i7/i5/i3 Desktop processors
System Speed	Up to 3.4GHz
Memory	2x 2GB DDR4-2133 SO-DIMM, Max. 32GB
Construction	Aluminum & steel
Chassis Color	Silver & Gray (Aluminum)
Front Panel External I/O	1x DVI-D + 1x VGA 1x Audio jack for MIC-in / Line-out 4x USB 2.0 ports 1x Red HDD LED 1x Power button with green LED indicator 1x CFast socket, 2x SIM card slots 1x 2-pin terminal block for external power button
Rear Panel External I/O	1x RS232/RS422/485 port for COM#1 3x RS232 port for COM#2/COM#3/COM#4 2x DisplayPort connector 1x RJ45 Gigabit Ethernet port + 2x USB 3.0 ports 1x RJ45 Gigabit Ethernet port + 2x USB 3.0 ports 1x 3 pin DC-in terminal block type for 12V~24V 2x Antenna holes
Expansion slots	2x Mini PCI-E sockets + 1x CFast slot
Storage	1x 2.5 SSD 2x mSATA (AMI220AF only) & 1x mSATA (AMI220EF only)
Mounting	Desktop or wall mount (wall mount kit included)
Dimensions	210mm (W) x 265mm (D) x 77mm (H)
Operating Temperature	-10°C to 70°C (14°F~158°F)*With Air flow -10°C to 50°C (14°F~122°F)*without Air flow
Storage Temperature	-20°C ~ 80°C (-4°F~176°F)
Relative Humidity	5~90% @ 45°C, (non-condensing)
Vibration	Non-Operating: 1.0 grms / 5~500Hz / random operation Operating: 0.25 grms / 5~500Hz / random operation
Shock	Operating : 20G/ 11ms; Non-Operating : 40G/ 11ms (MIL-STD-810G)
Certification	CE / LVD / FCC Class B

Ordering Information

AMI220AF	Fanless Box system with MB220AF, w/ Intel® Core™ i7/i5/i3 Desktop processor, 4x COM, 2x 4GB memory, 1x 2.5" 64GB MLC industrial-grade SSD, w/o power adaptor
AMI220EF	Fanless Box system with MB220EF, w/ Intel® Core™ i7/i5/i3 Desktop processor, 4x COM, 2x 4GB memory, 1x 2.5" 64GB MLC industrial-grade SSD, w/o power adaptor

Recommended Processor list

Model	TDP	Base Freq	Turbo Freq	Cache	Cores / Threads
i7-7700T	35W	2.9 GHz	3.8 GHz	8M	4/8
i7-6700TE	35W	2.4 GHz	3.4 GHz	8M	4/8
i5-7500T	35W	2.7 GHz	3.3 GHz	6M	4/4
i5-6500TE	35W	2.3 GHz	3.3 GHz	6M	4/4
i3-7101TE	35W	3.4 GHz	N/A	3M	2/4
i3-6100TE	35W	2.7 GHz	N/A	4M	2/4
G4400TE	35W	2.9 GHz	N/A	3M	2/2
G3900TE	35W	2.6 GHz	N/A	2M	2/2

Why AMI220?

Based on 7th/6th Gen. Intel® CPU (35W TDP)	Extreme Performance & Fanless	Supports 2x Mini PCI-E Expansion
Supports different type of Fieldbus through expansion	3x Gigabit LAN (Optional)	Flexible & Versatile Expansion Slot
Remote Power Button for Remote Access	SIM slot Redundancy	Supports RAID (0/1)
Wide-range voltage input (power protection)	Cableless Design	Wallmount, Desktop Mounting

1 Embedded Systems

2 CPU Modules

3 Disk-Size SBCs

4 Motherboards

5 CPU Cards

Dimensions and Drawing

