

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0014600095

Status:

Active

Overview:

SL Modular Connectors

Description:

2.54mm Pitch SL Insulation Displacement Connector Assembly, Female, Single Row, Version A, Non-polarized, Wire Size 28 AWG, 3.81µm Tin/Lead (SnPb), 9 Circuits

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Packaging Specification PK-70873-0001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		Ribbon Cable / Wire Trap Connectors
Series		70400
Comments		Terminals Preloaded
Component Type		Housing
Glow-Wire Capable		No
Overview		SL Modular Connectors
Product Name		SL
UPC		800753765634

Physical		
Circuits (Loaded)		9
Color - Resin		Black
Durability (mating cycles max)		25
Entry Angle		Vertical
Flammability		94V-0
Lock to Mating Part		None
Material - Metal		Phosphor Bronze
Material - Plating Mating		Tin
Material - Plating Termination		Tin
Material - Resin		Polyester Alloy
Number of Rows		1
PCB Retention		None
Packaging Type		Tube
Pitch - Mating Interface		2.54mm
Plating min - Mating		3.810µm
Plating min - Termination		1.905µm
Polarized to Mating Part		No
Stackable		Yes
Surface Mount Compatible (SMC)		N/A
Temperature Range - Operating		-40° to +105°C
Termination Interface: Style		IDT or Pierce
Wire Insulation Diameter		1.35mm max.
Wire Size AWG		28
Wire/Cable Type		Discrete Wire, Ribbon Cable

Electrical		
Current - Maximum per Contact		1.2A
Voltage - Maximum		250V

Material Info		
Engineering Number		70400-0358



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

70400 Series

Mates With

Single Row Headers and Housings, [8624](#) , [70203](#) , [42375](#) , [42377](#)

Use With

[7307](#) Tinned 28AWG, [7767](#) Topcoat 28AWG, [24241](#) Tinned 26AWG, [8996](#) Topcoat 26AWG, [24226](#) Tinned 24AWG, [8997](#) Topcoat 24AWG, [24369](#) High Flex 26AWG, [24389](#) High Flex 24AWG

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
IDT - Semi-automatic	11200949
- Bench-Top	
Terminator	

Reference - Drawing Numbers

Packaging Specification
Sales Drawing

PK-70873-0001-001
SDA-70400-0351-0374

Ribbon Cable Tool 622016600
Kit, Press Not
Included
Hawk Ribbon Cable 623003000
Terminator without
Break-off
Hawk Semi- 623003100
Automatic Discrete
Wire Terminator
Hawk Semi- 623004900
Automatic Discrete
Wire Terminator
for Rebuilt CE
Approved*
Hawk Flat Flex Cable623005200
Terminator with
Break-off
Hawk Ribbon Cable 623005300
Terminator with
Break-off

This document was generated on 07/28/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[14-60-0095](#)