

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022122284

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK 254 Solid Header, Right-Angle, with Friction Lock, 28 Circuits, 0.51µm Gold (Au) Plating

Documents:

- 3D Model

Packaging Specification PK-7478-001-000 (PDF)
- 3D Model (PDF)

Symbol Footprint Data SYM-22-05-3281-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-10-07-001 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

7478

Application

Signal, Wire-to-Board

Overview

KK Interconnect Solutions

Product Name

KK 254

UPC

800754930420

Physical

Breakaway

No

Circuits (Loaded)

28

Circuits (maximum)

28

Color - Resin

Natural (White)

Durability (mating cycles max)

50

Flammability

94V-0

Glow-Wire Capable

No

Lock to Mating Part

Yes

Material - Metal

Brass

Material - Plating Mating

Gold

Material - Plating Termination

Gold

Material - Resin

Nylon

Net Weight

3.693/g

Number of Rows

1

Orientation

Right Angle

PC Tail Length

3.58mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

2.54mm

Pitch - Termination Interface

2.54mm

Plating min - Mating

0.508µm

Plating min - Termination

0.508µm

Polarized to Mating Part

Yes

Polarized to PCB

Yes

Shrouded

Partial

Stackable

Yes

Temperature Range - Operating

See Product Specification

Termination Interface: Style

Through Hole

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

7478 Series

Mates With

2695 , 6471 , 7880 , 4455 , 7720

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	A-7478-28A241
Reference - Drawing Numbers	
Packaging Specification	PK-7478-001-000
Product Specification	PS-10-07-001
Sales Drawing	SDA-7478-000
Symbol/Footprint Data	SYM-22-05-3281-001

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[22-12-2284](#)