





- 1 THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POST AND HOUSING
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 PACKAGED IN SINGLE TUBES
- 4 POSTS: .000030 GOLD IN CONTACT AREA .000100-.000200 MATTE TIN LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 5 POSTS: .000030 GOLD IN CONTACT AREA .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

QTY	DESCRIPTION	DATE	BY	CHKD	APPD	REV	NO OF POSN	ASSEMBLY PART NUMBER
3	OBSOLETE						2	8-103166-6
6	OBSOLETE						36	8-103166-5
6	OBSOLETE						35	8-103166-4
6	OBSOLETE						34	8-103166-3
6	OBSOLETE						33	8-103166-2
6	OBSOLETE						32	8-103166-1
6	OBSOLETE						31	8-103166-0
6	OBSOLETE						30	7-103166-9
6	OBSOLETE						29	7-103166-8
6	OBSOLETE						28	7-103166-7
6	OBSOLETE						27	7-103166-6
6	OBSOLETE						26	7-103166-5
6	OBSOLETE						25	7-103166-4
6	OBSOLETE						24	7-103166-3
6	OBSOLETE						23	7-103166-2
6	OBSOLETE						22	7-103166-1
6	OBSOLETE						21	7-103166-0
6	OBSOLETE						20	6-103166-9
6	OBSOLETE						19	6-103166-8
6	OBSOLETE						18	6-103166-7
6	OBSOLETE						17	6-103166-6
6	OBSOLETE						16	6-103166-5
6	OBSOLETE						15	6-103166-4
6	OBSOLETE						14	6-103166-3
6	OBSOLETE						13	6-103166-2
6	OBSOLETE						12	6-103166-1
6	OBSOLETE						11	6-103166-0
6	OBSOLETE						10	5-103166-9
6	OBSOLETE						9	5-103166-8
6	OBSOLETE						8	5-103166-7
6	OBSOLETE						7	5-103166-6
6	OBSOLETE						6	5-103166-5
6	OBSOLETE						5	5-103166-4
6	OBSOLETE						4	5-103166-3
6	OBSOLETE						3	5-103166-2
6	OBSOLETE						2	5-103166-1
3	OBSOLETE						2	3-103166-6
6	OBSOLETE						36	3-103166-5
6	OBSOLETE						35	3-103166-4
6	OBSOLETE						34	3-103166-3
6	OBSOLETE						33	3-103166-2
6	OBSOLETE						32	3-103166-1
6	OBSOLETE						31	3-103166-0
6	OBSOLETE						30	2-103166-9
6	OBSOLETE						29	2-103166-8
6	OBSOLETE						28	2-103166-7
6	OBSOLETE						27	2-103166-6
6	OBSOLETE						26	2-103166-5
6	OBSOLETE						25	2-103166-4
6	OBSOLETE						24	2-103166-3
6	OBSOLETE						23	2-103166-2
6	OBSOLETE						22	2-103166-1
6	OBSOLETE						21	2-103166-0
6	OBSOLETE						20	1-103166-9
6	OBSOLETE						19	1-103166-8
6	OBSOLETE						18	1-103166-7
6	OBSOLETE						17	1-103166-6
6	OBSOLETE						16	1-103166-5
6	OBSOLETE						15	1-103166-4
6	OBSOLETE						14	1-103166-3
6	OBSOLETE						13	1-103166-2
6	OBSOLETE						12	1-103166-1
6	OBSOLETE						11	1-103166-0
6	OBSOLETE						10	103166-9
6	OBSOLETE						9	103166-8
6	OBSOLETE						8	103166-7
6	OBSOLETE						7	103166-6
6	OBSOLETE						6	103166-5
6	OBSOLETE						5	103166-4
6	OBSOLETE						4	103166-3
6	OBSOLETE						3	103166-2
6	OBSOLETE						2	103166-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN H MOLL 27JUL87		TE Connectivity NAME: HDR ASSY, MOD II, SHROUDED, 4 SIDES, DBL ROW, .100X.100 RIGHT ANGLE, W/ .025 SQ POSTS	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		FINISH: SEE TABLE MATERIAL: HOUSING: PHOSPHOR BRONZE POSTS: PHOS BRONZE		APPLICATION SPEC: --- SIZE: A1 CAGE CODE: 00779 DRAWING NO: 103166 WEIGHT: --- CUSTOMER DRAWING: ---	
SCALE: 4:1 SHEET: 1 OF 1 REV: K2				RESTRICTED TO: ---	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-103166-1](#)